

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

98mm Max. Aperture, Iris Diaphragm



Stock #32-611 3-4 DAYS



1



€397,00

ADD TO CART

Qty 1-4

€397,00

Qty 5+

€350,60

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
5.0

Maximum Aperture (mm):
98.0

Outer Diameter (mm):

130.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 20.00
Number of Leaves: 20.00
Thickness (mm): 12.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)