

140mm Length, Adjustable Laser Holder



#56-332, #56-333

Stock **#56-332** 5 In Stock

-

1

+

€375⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€375,00 each
Qty 5-25	€331,50 each
Qty 26-49	€305,30 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Adjustable - Tilt

Type:

Cylindrical Tube

Type of Optics:

Physical & Mechanical Properties

Length (mm):

140.00	
740	Weight (g):
Black Anodized Aluminum	Construction:
0.5	Twin Ring Mount Adjustment Screw Pitch (mm):
±4	Tilt Angle (°):
Threading & Mounting	
20.0 - 55.0	Size of Compatible Optics (mm):
M6 x 1.0	Compatible Post:
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	Reach 247:

Product Details

- Twin Ring Mount Design
 - Fixed and Adjustable Versions
 - Ideal for He-Ne Lasers
 - [Posts](#) and [Post Holders](#) Required for Mounting
- Designed for [Helium-Neon Lasers](#), this mount is ideal for any optical tube assembly. [Posts](#) and [Post Holders](#) are required for mounting to a breadboard.
- Mounting hole is M6 x 1.0

Technical Information

