

[See all 7 Products in Family](#)

14.5mm Dia x 21mm FL, Grade 1, Plano-Convex Lens



Stock #28-384 CLEARANCE **1 In Stock**

⊖ 1 ⊕ €10⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€10,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

14.50 **Diameter (mm):**

Optical Properties

21.00 **Effective Focal Length EFL (mm):**

1.45

f#:

0.34

Numerical Aperture NA:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Plano-convex (PCX) lenses have one flat and one outward curved face. They have a positive focal length, making them ideal for collecting and focusing light in imaging applications.

1 - 24.9mm Experimental Quality Plano-Convex (PCX) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

