

8mm Max. Aperture, Burnished Steel Leaves Iris Diaphragm



Standard Series

Stock #57-580 3-4 DAYS

⊖ 1 ⊕ **€70,00**

ADD TO CART

Qty 1-4
€70,00
Qty 5+
€61,70
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.0, Typical

Maximum Aperture (mm):
8.0

Outer Diameter (mm): 14.8
Construction: Anodized Aluminum Alloy, Burnished Spring Steel Leaves
Lever Diameter (mm): 1.50
Lever Length (mm): 6.00
Number of Leaves: 9
Thickness (mm): 4.50

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant