

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #24-717 CLEARANCE 3-4 DAYS



1



€216,95

ADD TO CART

Qty 1+

€216,95

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
14.00 ±0.01

Substrate: ☐
Calcium Fluoride (CaF₂), IR Grade

Coating:
Uncoated

Type:
Half-Ball Lens

Wavelength Range (nm): 300 - 8000
Center Thickness CT (mm): 7.00 ±0.05
Index of Refraction n_d: 1.434
Model Number: CF-HS-14
Radius R (mm): 7.00
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View