


1.5 OD 50mm Sq, Absorptive ND Filter

See More by [Hoya](#)



Stock **#48-096** 3-4 DAYS

- 1 + **€95,00**

ADD TO CART

Qty 1-10
€95,00
Qty 11+
€84,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):

1.5 ±0.05
Glass/Filter Number: Hoya ND-0.3
Substrate: ☐ ND Filter Glass
Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 490
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 3.0 (average)
Type: Neutral Density Filter
Width (mm): 50.00
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.2
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View