

**TECHSPEC®** 15 x 15mm Enhanced Aluminum, λ/4 Mirror



Stock **#45-725** ☐ In Stock

1  **€52,50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €52,50                        |
| Qty 6+                        |
| €42,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):  
λ/4

Substrate: ☐  
[BOROFLOAT®](#)

Back Surface:  
Commercial Polish

|                                                                                         |
|-----------------------------------------------------------------------------------------|
| <b>Surface Quality:</b><br>60-40                                                        |
| <b>Dimensions (mm):</b><br>15.0 x 15.0                                                  |
| <b>Dimensional Tolerance (mm):</b><br>±0.25                                             |
| <b>Coating Specification:</b><br>R <sub>avg</sub> >95% @450 - 650nm                     |
| <b>Coating:</b><br>Enhanced Aluminum (450-650nm)                                        |
| <b>Coating Type:</b><br>Metal                                                           |
| <b>Bevel:</b><br>Protective bevel as needed                                             |
| <b>Clear Aperture (%):</b><br>85                                                        |
| <b>Edges:</b><br>Fine Ground                                                            |
| <b>Thickness (mm):</b><br>2.00 ±0.25                                                    |
| <b>Type:</b><br>Flat Mirror                                                             |
| <b>Wavelength Range (µm):</b><br>0.45 - 0.65                                            |
| <b>Wavelength Range (nm):</b><br>450 - 650                                              |
| <b>Length (mm):</b><br>15.00                                                            |
| <b>Width (mm):</b><br>15.00                                                             |
| <b>Damage Threshold, Reference:</b> <input type="checkbox"/><br>0.2 J/cm² @ 532nm, 10ns |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |