

15 x 21.21 x 2mm Elliptical Beamsplitter 50R/50T



Stock **#27-608** CLEARANCE 3-4 DAYS

- 1 + **€24,95**

ADD TO CART

Qty 1+
€24,95

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture (%) : 80.00
Coating Specification : Surface 1: Dielectric, ±5% R/T @ 550nm Surface 2: AR ¼λ MgF ₂ @ 550nm
Dimensional Tolerance (mm) : ±0.25
Dimensions (mm) : 15.0 x 21.21
Major Axis (mm) :

21.21
Minor Axis (mm): 15.00
Reflection (%): 50.00
Substrate: N-BK7
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.25
Transmission (%): 50.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
