

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #22-712 3-4 DAYS

[Other Coating Options](#)



1



€2.250,00

ADD TO CART

Qty 1-5

€2.250,00

Qty 6+

€1.800,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):

150.00 +0.0/-0.1

Effective Focal Length EFL (mm):

120.00 @587.6nm

Numerical Aperture NA:

0.63
Back Focal Length BFL (mm): 92.86
Substrate: N-SF5
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 128
Edge Thickness ET (mm): 7.30
Center Thickness CT (mm): 45.40 ±0.1
f#: 0.80
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 380 - 2500
Conjugate Distance: Infinite
Power (diopters): 8.33

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant