

TECHSPEC®

# 15.0mm Dia. x 75.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-360** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€29,00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| €29,00                        |
| Qty 10+                       |
| €26,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):

|                                                |
|------------------------------------------------|
| 75.00 @ 587.6nm                                |
| <b>Back Focal Length BFL (mm):</b><br>73.79    |
| <b>Coating:</b><br>Uncoated                    |
| <b>Substrate:</b> <a href="#">N-BK7</a>        |
| <b>Surface Quality:</b><br>40-20               |
| <b>Power (P-V) @ 632.8nm:</b><br>1.5λ          |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>λ/4    |
| <b>Focal Length Tolerance (%):</b><br>±1       |
| <b>Centering (arcmin):</b><br><1               |
| <b>Center Thickness CT (mm):</b><br>1.83 ±0.10 |
| <b>Edge Thickness ET (mm):</b><br>1.10         |
| <b>Radius R<sub>1</sub> (mm):</b><br>38.76     |
| <b>Clear Aperture CA (mm):</b><br>14           |
| <b>f/#:</b><br>5                               |
| <b>Numerical Aperture NA:</b><br>0.10          |
| <b>Type:</b><br>Plano-Convex Lens              |
| <b>Bevel:</b><br>Protective bevel as needed    |
| <b>Wavelength Range (nm):</b><br>350 - 2200    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |