

[All Products](#) / [Imaging Lenses](#) / [Ruggedized Lenses](#) / [Athermal Imaging Lenses](#)

[See all 6 Products in Family](#)



Stock **#16-854** 3-4 DAYS

1

+

€1.695,00

ADD TO CART

Qty 1+

€1.695,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
143.30

Horizontal Field of View, 1/2" Sensor:
2.44°

Horizontal Field of View, 2/3" Sensor:
3.36°

Maximum Diameter (mm):
60.0

Operating Temperature (°C): -10 to +50
Horizontal Field of View, 1" Sensor: 4.87°
Maximum Image Circle (mm): 17.60
Numerical Aperture NA, Object Side: 0.002
Horizontal Field of View, 1.1" Sensor: 5.36°
Number of Elements (Groups): 7 (3)
Horizontal Field of View, 1/1.8" Sensor: 2.75°
Type: Fixed Focal Length Lens - Athermal
Focal Length FL (mm): 150.00
Primary Magnification PMAG: 0.000X - 0.040X
Maximum Sensor Format: 1.1"
Working Distance (mm): 4000 - ∞
Mount: C-Mount
Aperture (f/#): f/8
Entrance Pupil Position (mm): 15.323
Object Space Principal Plane (mm): -93.76
Image Space Principal Plane (mm): -42.27
Field of View at Max Sensor Format: Horizontal: 5.36° Vertical: 4.03° Diagonal: 6.68°
Maximum Distortion (%): 0.66
Exit Pupil Position (mm): -37.311
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View