

152.4mm Standard Res Image Conduit with 100µm Fibers



Stock #38-307 3-4 DAYS

⊖ 1 ⊕ **€269,00**

ADD TO CART

Qty 1-4

€269,00

Qty 5+

€237,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Bend Radius (mm):
25.6

Diameter Tolerance (inches):
±0.010

Length (mm):
152.40

Numerical Aperture NA:
0.53

Number of Fibers:
3012.00

Operating Temperature (°C):
454.00

Outer Diameter (mm):
6.40

Resolution:
5 lp/mm

Transformation Temperature (°C):
704.00

Transmission (%):
35 - 45

Fiber Diameter (µm):
100.00

Type:
Standard Resolution

Length Tolerance (inches):
±0.030

Packing Fraction (%):
100.00

Index of Refraction n_d - Core:
1.58

Index of Refraction n_d - Cladding:
1.49

Wavelength Range (nm):
350 - 1500

Regulatory Compliance

RoHS:
[Exempt](#)

Certificate of Conformance:
[View](#)
