

152.4mm Standard Res Image Conduit with 50µm Fibers



Stock #40-642 3-4 DAYS

- 1 + **€202,00**

ADD TO CART

Qty 1-4
€202,00
Qty 5+
€177,90
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Minimum Bend Radius (mm): 12.8
Diameter Tolerance (inches): ±0.010
Length (mm): 152.40
Numerical Aperture NA:

0.53
Number of Fibers: 3012.00
Operating Temperature (°C): 454.00
Outer Diameter (mm): 3.20
Resolution: 10 lp/mm
Transformation Temperature (°C): 704.00
Transmission (%): 35 - 45
Fiber Diameter (µm): 50.00
Type: Standard Resolution
Length Tolerance (inches): ±0.030
Packing Fraction (%): 100.00
Index of Refraction n_d - Core: 1.58
Index of Refraction n_d - Cladding: 1.49
Wavelength Range (nm): 350 - 1500

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View