

1.55" ID, Fiber Optic Ring Light Guide



Stock #54-174 3-4 DAYS

1 **€678,00**

ADD TO CART

Qty 1+

€678,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Acceptance Angle (°):
68.00

C'Bore Diameter (inches):
1.550

Minimum Bend Radius (mm):
38.1

Ferrule Diameter (inches): 0.562
Fiber Bundle Diameter (inches): 0.333
Length (inches): 36
Numerical Aperture NA: 0.55
Operating Temperature (°C): -40 to +107
Outer Diameter (inches): 2.562
Output Beam Angle (°): 5.00
PVC Sheathing: Metal Hose
Fiber Diameter (µm): 50.00
Inner Diameter (inches): 1.550
Working Distance (inches): 2.7-4.5
Length Tolerance (inches): ±0.5
Packing Fraction (%): 82% nominal
Index of Refraction n_d - Core: 1.581
Index of Refraction n_d - Cladding: 1.487
Transmission Loss: 6% per ft. at 600nm
Type of Illumination: Fiber Optic Light Guide
Compatible Light Guide Adapter: SX: #38-946 MX: #66-908
Wavelength Range (nm): 400 - 2000
Geometry: Ring Light

Regulatory Compliance

Reach 174: Compliant
RoHS: Not Compliant
Certificate of Conformance: View