

TECHSPEC® 15mm Aluminum & UV-VIS, Ultra Precision UV Fused Silica Right Angle Prism



Stock **#39-843** 3-4 DAYS

⊖ 1 ⊕ **€312,00**

ADD TO CART

Qty 1-5

€312,00

Qty 6+

€280,80

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
UV-VIS & Aluminized

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 21.20
Length of Legs (mm): 15.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: Legs: $R_{\text{abs}} \leq 1.0\%$ @ 350 - 450nm, $R_{\text{avg}} \leq 1.5\%$ @ 250 - 700nm Hypotenuse: $R_{\text{avg}} > 85\%$ @ 400 - 700nm, $R_{\text{avg}} > 90\%$ @ 400 - 2000nm w/Black Overpaint
Wavelength Range (nm): 250 - 700
Surface Flatness (P-V): $\lambda/20$
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm^2 @ 532 & 1064nm, 10ns Legs: 3 J/cm^2 @ 355nm, 10ns; 5 J/cm^2 @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant