

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

15mm Dia. Left-Handed VIS-Coated Glass Circular Polarizer (CP42HE)



Stock #19-933 3-4 DAYS

- 1 + €52,00

ADD TO CART

Qty 1-9
€52,00

Qty 10+
€47,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
VIS AR Coated

Diameter (mm):
15.00

Substrate: ☐
[Polymer Film CP42HE](#) Laminated Between Glass

Operating Temperature (°C): -40 to +80
Thickness (mm): 2.00 ±0.10
Transmission (%): 45 ±2
Type: Left-Handed Circular Polarizer
Dimensional Tolerance (mm): ±0.20
Construction: Laminated Glass Polarizing Film
Coating Specification: R _{avg} <0.5% @ 425 - 700nm
Wavelength Range (nm): 425 - 700
Polarization Efficiency (%): >99.90

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant