

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [Optotune](#)



Stock #14-575 3-4 DAYS



1



€2.544,00

ADD TO CART

Qty 1+

€2.544,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Model Number:
MR-15-30-G-25x25D

Diameter (mm):

15.00
Housing Diameter (mm): 45
Coating: Protected Gold
Coating Specification: R _{avg} >97% @ 800 - 20,000nm
Surface Quality: 60-40
Mechanical Tilt (°): ±25
Repeatability (μrad): 30 - 100 RMS
Storage Temperature (°C): -40 to +85
Operating Temperature (°C): 0 to +40
Operating System: Windows® 10
Power Requirement: 15 - 28 VDC
Power Supply: Power Supply Required and Sold Separately. USA: #14-576 Europe: #14-576 Japan: Not Available Korea: Not Available China: #14-576
Note: Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.
Scan Angle (°): ±25 (Mechanical) ±50 (Optical)
Step Response 0.1° (ms): 2
Step Response 20° (ms): 12

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View