

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

15mm Dia. x 22.5mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-083 CLEARANCE 3-4 DAYS



1



€19,95

ADD TO CART

Qty 1+

€19,95

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.00 +0.00/-0.10

Effective Focal Length EFL (mm):
22.50

Back Focal Length BFL (mm):
20.37

Coating:
MgF₂ (400-700nm)

Coating Specification:
R_{avg} ≤1.75% @400 - 700nm

Substrate: ☐ N-SK18
Focal Length Tolerance (%): ±1
Centering (arcmin): 6.00
Edge Thickness ET (mm): 1.39
Radius R₁ (mm): 14.37
Clear Aperture CA (mm): 14.00
f/#: 1.5
Numerical Aperture NA: 0.33
Type: Plano-Convex Lens

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View