

[See all 5 Products in Family](#)

15mm Dia. x 30mm FL, Commercial Grade, Plano-Convex Lens



Stock #23-085 CLEARANCE **20+ In Stock**

⊖ 1 ⊕ €20^{.50}

ADD TO CART

Volume Pricing

Qty 1+	€20,50 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens **Type:**

Physical & Mechanical Properties

15.00 +0.00/-0.10 **Diameter (mm):**

6.00 **Centering (arcmin):**

1.27 **Edge Thickness ET (mm):**

Clear Aperture CA (mm):
14.00

Optical Properties

Effective Focal Length EFL (mm):
30.00

Coating:
MgF₂ (400-700nm)

Coating Specification:
R_{avg} ≤ 1.75% @ 400 - 700nm

Substrate: □
N-SK18

Focal Length Tolerance (%):
±1

Radius R₁ (mm):
19.16

f#:
2.00

Numerical Aperture NA:
0.25

Regulatory Compliance



Certificate of Conformance:
[View](#)

Product Details

- Feature Standard Designs and Specifications
- Also Available [Uncoated](#)
- For More Options, View [Precision Quality Plano-Convex \(PCX\) Lenses](#)

Plano convex lenses (PCX) have one flat and one outward curving face and a positive focal length. They are ideal for collecting and focusing light in imaging applications. They are also useful in a variety of applications involving emitters, detectors, lasers, and fiber optics. MgF₂ anti-reflection coating offers improved transmission in the visible spectrum. Commercial Grade MgF₂ Coated Plano-Convex (PCX) Lenses offer commercial quality, at an affordable price.

Technical Information



Coating Curves