


TECHSPEC® 15mm Dia. x 30mm FL, MgF₂ Coated, Plano-Convex Lens



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-209** 3-4 DAYS

- 1 +

€140,00

ADD TO CART

Qty 1-5

€140,00

Qty 6+

€112,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
15.00 -0.025

Effective Focal Length EFL (mm):

30.00 @ 587.6nm
Back Focal Length BFL (mm): 27.53
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 3 Rings
Irregularity (P-V) @ 632.8nm: 0.5 Rings
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.60 ± 0.10
Edge Thickness ET (mm): 1.38
Radius R₁ (mm): 13.75
Clear Aperture CA (mm): 14
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant