

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-531 3-4 DAYS

[Other Coating Options](#)



1



€58,00

ADD TO CART

Qty 1-10

€58,00

Qty 11+

€51,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
15.00 +0.1/-0.3

Effective Focal Length EFL (mm):
12.00

Numerical Aperture NA:
0.63

Back Focal Length BFL (mm): 8.2
Substrate: B270
Focal Length Tolerance (%): ±7
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 14
Edge Thickness ET (mm): 2.0
Center Thickness CT (mm): 7.50 ±0.2
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 15.0
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant