

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

15" X 15" , 0.090" FL, Lenticular Array



Stock #43-027 3-4 DAYS



1



€263,00

ADD TO CART

Qty 1-10

€263,00

Qty 11+

€229,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):

2.29

Substrate: ☐

Acrylic

Coating:

Uncoated

Type:

Lens Array
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.09
Center Thickness CT (mm): 2.30
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 15 x 15
Dimensions (mm): 381 x 381
Effective Focal Length EFL (inches): 0.09
Effective Size (inches): 15 x 15
Index of Refraction n_d: 1.49
Number of Lenses: 53 per 25.4mm
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Thickness Tolerance (mm): ±0.92

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View