

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 16.25" Diameter x 80" FL Uncoated, Parabolic Mirror



Stock #32-725-000 3-4 DAYS

1 €6.993,00

ADD TO CART

Qty 1-2

€6.993,00

Qty 3+

€5.944,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: BOROFLOAT® SUPREMAX®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 16.25 +0.06/-0
Diameter (mm): 412.80 +1.5/-0
Effective Focal Length EFL (inches): 80.0
Effective Focal Length EFL (mm): 2,032.00
Radius of Curvature (mm): 4,064.00
Aperture (f/#): f/4.9
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 372
Edge Thickness ET (inches): 3.25
Edge Thickness ET (mm): 82.60
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View