

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

165mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-181 3-4 DAYS



1



€866,00

ADD TO CART

Qty 1-4

€866,00

Qty 5+

€779,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
165.10

Maximum Diameter (mm):
109

Scan Angle (°):

±28.50
Scan Field (mm): 116.2 x 116.2
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Type: F-Theta Lens
Working Distance (mm): 188.1
Wavelength Range (nm): 1064
Flange Distance (mm): 219.1
Focus Size Diameter, 1/e² (µm): 26
Input Beam Diameter, 1/e² (mm): 12
Maximum Length (mm): 54.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View