

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

16mm Dia. x 10.8mm FL, MgF<sub>2</sub> Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock #35-047 [CONTACT US](#)

[Other Coating Options](#)



1



€42,50

ADD TO CART

Qty 1-10

€42,50

Qty 11+

€37,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
16.00 +/-0.3

Effective Focal Length EFL (mm):  
10.80 @ 587.6nm

Numerical Aperture NA:  
0.74

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>5.90                                                                      |
| <b>Substrate:</b> <a href="#">N-F2</a>                                                                          |
| <b>Focal Length Tolerance (%):</b><br>±5                                                                        |
| <b>Coating:</b><br>MgF <sub>2</sub> (400-700nm)                                                                 |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤ 1.75% @ 400 - 700nm                                         |
| <b>Centering (arcmin):</b><br>≤25                                                                               |
| <b>Surface Quality:</b><br>Molded Side: 5/3 x 0.4; E 0.2<br>Polished Side: 5/3 x 0.25; E 0.2                    |
| <b>Clear Aperture CA (mm):</b><br>12.80                                                                         |
| <b>Edge Thickness ET (mm):</b><br>2.6                                                                           |
| <b>Center Thickness CT (mm):</b><br>8.00 ±0.20                                                                  |
| <b>f#:</b><br>0.68                                                                                              |
| <b>Bevel:</b><br>Protective bevel as needed                                                                     |
| <b>Diameter of Asphere (mm):</b><br>16.0                                                                        |
| <b>Radius R<sub>2</sub> (mm):</b><br>Plano                                                                      |
| <b>Shape of Back Surface:</b><br>Plano                                                                          |
| <b>Type:</b><br>Condenser Lens                                                                                  |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                      |
| <b>Conjugate Distance:</b><br>Infinite                                                                          |
| <b>Note:</b><br><a href="#">Click here</a> for more information on the ISO 10110 surface quality specification. |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |