

18 x 30mm, 25R/75T, Plate Beamsplitter



Stock #46-687 3-4 DAYS

⊖ 1 ⊕ **€47,00**

ADD TO CART

Qty 1-9

€47,00

Qty 10+

€33,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture (%):
>85

Coating Specification:
Surface 1: Dielectric, ±5% RT @ 550nm
Surface 2: Uncoated

Construction:

Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm):
18.0 x 30.0

Edges:
Cut

Reflection/Transmission Ratio (R/T):
25/75

Substrate: □
Float Glass

Surface Flatness (P-V):
4 - 6λ

Surface Quality:
80-50

Thickness (mm):
2.00

Type:
Standard Beamsplitter

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
