

18 x 30mm, 40R/60T, Plate Beamsplitter



Stock **#46-689** 3-4 DAYS

⊖ 1 ⊕ **€47,00**

ADD TO CART

Qty 1-9
€47,00

Qty 10+
€33,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: Uncoated

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 18.0 x 30.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 40/60
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 2.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant