

1800 Grooves/mm, 12.7mm Square, VIS Holographic Grating



Reflective Holographic Gratings

Stock #43-775 3-4 DAYS



1



€102,00

ADD TO CART

Qty 1+

€102,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1800

Wavelength Range (nm):
400 - 700

Dimensions (mm):
12.7 x 12.7 ±0.5

Coating:
Bare Aluminum

Construction: Holographic Grating
Length (mm): 12.70
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Wavelength: VIS
Width (mm): 12.70
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%): 81
Peak Efficiency Avg, Typical (%): >65

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
