

TECHSPEC®

18.0mm Dia. x 25.0mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock #38-314-INK

CONTACT US

[Other Coating Options](#)

-

1

+

€52,50

ADD TO CART

Qty 1-9
€52,50
Qty 10+
€47,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
18.00 ±0.025

Effective Focal Length EFL (mm):

25.00 @ 587.6nm
Back Focal Length BFL (mm): 21.51
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.30 ±0.10
Edge Thickness ET (mm): 1.65
Radius R₁ (mm): 12.92
Clear Aperture CA (mm): 17
f/#: 1.39
Numerical Aperture NA: 0.36
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View