

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 180mm EFL Uncoated, UV-to-NIR Corrected Triplet



Stock #47-313 [CONTACT US](#)

- 1 + **€2.369,00**

ADD TO CART

|           |
|-----------|
| Qty 1-5   |
| €2.369,00 |

|           |
|-----------|
| Qty 6+    |
| €2.014,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):  
180.00

Focal Length Tolerance (%):  
±1.5 @ 248nm

Back Focal Length BFL (mm):  
174.62

Back Focal Length BFL from Housing (mm):

|                                                                                                                  |
|------------------------------------------------------------------------------------------------------------------|
| 172.3                                                                                                            |
| <b>Clear Aperture CA (mm):</b><br>22.5                                                                           |
| <b>Substrate:</b> <input type="checkbox"/><br>CaF <sub>2</sub> / <a href="#">Fused Silica</a> / CaF <sub>2</sub> |
| <b>Surface Quality:</b><br>60-40                                                                                 |
| <b>f#:</b><br>8.00                                                                                               |
| <b>Numerical Aperture NA:</b><br>0.06                                                                            |
| <b>Coating:</b><br>Uncoated                                                                                      |
| <b>Effective Focal Length EFL @ 248nm (mm):</b><br>180.00                                                        |
| <b>Housing Diameter (mm):</b><br>30.00 ±0.05                                                                     |
| <b>Housing Length (mm):</b><br>20.50 ±0.05                                                                       |
| <b>Type:</b><br>Achromatic Triplet Lens                                                                          |
| <b>Wavelength Range (nm):</b><br>193 - 1000                                                                      |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |