

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

138mm Max. Aperture, Iris Diapnragm



Stock #32-608 □ In Stock



1



€622,00

ADD TO CART

Qty 1-4

€622,00

Qty 5+

€548,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
11.5

Maximum Aperture (mm):
138.0

Outer Diameter (mm):

180.0
Construction: Aluminum Housing, Blue Tempered Spring Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 19.10
Number of Leaves: 20.00
Thickness (mm): 13.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)