

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #22-843 3-4 DAYS

[Other Coating Options](#)



1



€46,00

ADD TO CART

Qty 1-10

€46,00

Qty 11+

€42,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
18.00 +0.0/-0.2

Effective Focal Length EFL (mm):
15.50

Numerical Aperture NA:
0.58

Back Focal Length BFL (mm): 10.87
Substrate: ☐ H-K9L
Focal Length Tolerance (%): ±8
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 80-50 (typical)
Clear Aperture CA (mm): 16.20
Edge Thickness ET (mm): 1.44
Center Thickness CT (mm): 7.00 ±0.30
f/#: 0.86
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 18.00
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View