

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



YAG-BBAR Coated Double-Convex (DCX) Lenses



Stock #89-256-INK [CONTACT US](#)

− 1 +

€57,00

ADD TO CART

Qty 1-9

€57,00

Qty 10+

€51,25

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
18.00 ±0.025

Back Focal Length BFL (mm):

34.59
Effective Focal Length EFL (mm): 36.00
Coating: YAG-BBAR (500-1100nm)
Coating Specification: R _{abs} <0.25% @ 532nm R _{abs} <0.25% @ 1064nm R _{avg} <1.0% @ 500 - 1100nm
Substrate: 
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 4.80
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.55
Radius R₁=R₂ (mm): 36.6
Clear Aperture CA (mm): 17.00
f/#: 2.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.25
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View