


18mm Dia x -46 FL MgF₂ Coated, Achromatic Lens



Stock #30-448 CLEARANCE **20+ In Stock**

€14^{.50}

ADD TO CART

Volume Pricing	
Qty 1+	€14,50 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

18.00 **Diameter (mm):**

Optical Properties

-46.00 **Effective Focal Length EFL (mm):**

2.56 f#:

0.20 Numerical Aperture NA:

MgF₂ (400-700nm) Coating:

R_{avg} ≤ 1.75% @ 400 - 700nm Coating Specification:

400 - 700 Wavelength Range (nm):

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Correct for Color and On-Axis Aberrations
- MgF₂ Coated for Low Reflection
- Ideal for use as Barlow Lenses

Consisting of two optical elements cemented together, negative achromats are corrected for color and on-axis aberrations. Used predominantly as Barlow lenses to extend focal lengths, they are often combined with positive achromatic mirror systems and imaging lenses.

Coating Curves