

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #36-183 ☒ In Stock



1



€59,00

ADD TO CART

Qty 1-49

€59,00

Qty 50+

€47,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
15.70

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
4.50

Horizontal Field of View @ Max Sensor Format:

122
Resolution, On-Axis: 160 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 80 lp/mm @ 20% Contrast
Resolution, Full Field: 107 lp/mm @ 20% Contrast
Note: IR Cut-Off Filter Included
Type: M12 Imaging Lens
Focal Length FL (mm): 1.80
Maximum Sensor Format: 1/4"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mount)
Aperture (f/#): f/2
Distortion (%): -76.2
IR Cut Filter: Yes
Lens Wavelength Range: VIS (IR-Cut Filter)

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View