

## 5mW, 635nm Laser Bat Power ZAT



Stock **#19-444** **1 In Stock**

- 1 + €258<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€258,00 each
Qty 10+	€232,00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes



## General

Elliptical Dot  
Style:  
3R  
Laser Class - CDRH:

## Physical & Mechanical Properties

162  
Weight (g):  
124.00  
Length (mm):

## Optical Properties

635.00  
Wavelength (nm):  
Red  
Color:  
Up to 2,000mm  
Focus Range (mm):

## Electrical

5  
Output Power (mW):

## Hardware & Interface Connectivity

1 AA Battery (Not Included)  
Power Requirement:  
Free Space  
Output Type:

## Environmental & Durability Factors

IP40  
Environmental Rating:

## Regulatory Compliance

[View](#)  
Certificate of Conformance:

## Product Details

- Bright Red 635nm Wavelength
- Line, Crosshair, or Dot Projection
- Battery Powered Operation with a Fixed Focus
- Sturdy, Metal Housing

Z-Laser ZAT Battery Powered Lasers are ideal for positioning and alignment applications. Their battery powered design provides maneuverability by removing the need for a fixed power supply. IP40 rated, shock proof, and vibration proof with a sturdy, metal housing makes these lasers excellent for harsh environments and repeated use. Z-Laser ZAT Battery Powered Lasers are suitable for use in industrial environments such as Automotive, Paper, Wood, Ceramic, and Metal. Available with 1 or 5mW output powers, the lasers utilize one AA battery (not included) ensuring easy maintenance and an extended lifetime.