

TECHSPEC® 1" Dia, 3" FL Uncoated, Spherical Mirror



Stock #43-341 3-4 DAYS

⊖ 1 ⊕ **€98,00**

ADD TO CART

Qty 1-9

€98,00

Qty 10+

€83,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: **BOROFLOAT®**

Focal Length Tolerance (%):
±2

Surface Quality:
60-40

Surface Accuracy:

λ/4

Diameter (inches):

1.0

Diameter (mm):

25.40 +0/-0.3

Diameter Tolerance (inches):

+0/-0.01

Effective Focal Length EFL (inches):

3.00

Effective Focal Length EFL (mm):

76.20

Radius of Curvature (mm):

152.40

Aperture (f/#):

f/3

Coating:

Uncoated

Coating Type:

Uncoated

Back Surface:

Ground

Edge Thickness ET (inches):

0.25

Edge Thickness ET (mm):

6.35

Edge Thickness Tolerance (%):

+0.0/-15

Type:

Spherical Mirror

Regulatory Compliance

RoHS 2015:[Compliant](#)**Reach 219:**[Compliant](#)**Certificate of Conformance:**[View](#)