

1" Travel, Eng Micrometer, Thru-Hole 2.62" Stage



Stock #38-203 3-4 DAYS

- 1 + **€1.193,00**

ADD TO CART

Qty 1+
€1.193,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Digital Micrometer (English)

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm): 66.5 x 66.5
Travel (inches): 1
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (inches): 0.00005
Load Capacity, Normal (lbs): 62
Load Capacity, T_a (lbs): 10
Load Capacity, T_b (lbs): 2
Note: Thru-Hole
Stage Size (inches): 2.62 x 2.62
Straight Line Accuracy (inches): 0.00008 per inch of travel
Weight (lbs): 1.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View