

2.00", English Rotary Stage



Stock #33-465 **2 In Stock**

-

1

+

€983^{.65}

ADD TO CART

Volume Pricing	
Qty 1+	€983,65 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:

English

Physical & Mechanical Properties

Weight (lbs):

44.4 x44.4	Stage Size (mm):
1.75 x 1.75	Stage Size (inches):
Aluminum top and base; steel tangent arm drive	Construction:
0.25" Dia. Thru	Center Hole:
±5 (Fine), 360 (Coarse)	Travel (°):
12	Increments (arcmin):
10	Load Capacity, Normal (lbs):
4	Load Capacity, Vertical (lbs):
Rotary	Type of Movement:
Ball Bearing	Guide System:
2	Table Diameter (inches):

Hardware & Interface Connectivity

Tangent Arm	Type of Drive:
-------------	----------------

Threading & Mounting

(12) 6-32 on 0.625", 1.125" & 1.50" dia. B.C.	Mounting Threads:
---	-------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

PRODUCT DETAILS

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
 - 2 or 2.62" Diameter Stages with Tapped Mounting Holes
 - Calibrated Dial with 12 Minute Vernier for Accurate Read-Out
- Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

TECHNICAL INFORMATION



