

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



2" Travel, 3"L x 1.75"W Ball Bearing Slide, #37-361

Stock #37-361 3-4 DAYS



1



€226,00

ADD TO CART

Qty 1+

€226,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Manual

Type:
English

Stage Size (mm):

44.4 x 76.2
Travel (inches): 2
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Height (inches): 0.75
Load Capacity, Normal (lbs): 40.0
Mounting Threads: (12) 6-32 on Top
S.H.C.S. C'bore: (2) #6 on Base
Stage Size (inches): 1.75 x 3.00
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
