

2" x 2" White Edge-Lit Backlight

See More by [Advanced Illumination](#)



Stock #73-893 NEW **1 In Stock**

€625⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	€625,00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Model Number:
BX2-050050WH1IC

LED Lifetime (hours):
50,000

Type of Illumination:
LED Illuminator

Manufacturer:
Advanced Illumination

Backlight **Geometry:**

Constant **Illumination Mode:**

Physical & Mechanical Properties

106.7 L x 106.7 W x 19.1 T **Dimensions (mm):**

2 x 2 **Active Area (inches):**

Optical Properties

White **Color:**

Hardware & Interface Connectivity

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

Environmental & Durability Factors

0 - 35 **Operating Temperature (°C):**

Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Contains SVHC\(s\)](#) **Reach 247:**

Product Details

- 30% Brighter than Comparable Surface Mount Light
- Uniform, Low Heat Illumination

Advanced Illumination Side-Fired LED Backlights are high performance alternatives to surface mount lights. Advanced Illumination Side-Fired LED Backlights provide uniform, low heat illumination that is 30% brighter than surface mount lights of equal size. To simplify system integration, these backlights include mounting brackets and mounting channels for M6 nuts.

Note: Required 24V power supply [#66-855](#). [Accessories for Advanced Illumination products](#) are available and sold separately. Units cannot be intensity controlled.