

20 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock #59-546 **2 In Stock**

- 1 + €316⁰⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-4 | €316,00 each |
| Qty 5+ | €301,50 each |
| Need More? | Request Quote |

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Pattern Location is Centered

Note:

No

NIST Certification:

Physical & Mechanical Properties

±0.100

Dimensional Tolerance (inches):

| | |
|-------------|-----------------------------------|
| 25.40 | Length (mm): |
| 12.7 x 25.4 | Pattern Size (mm): |
| 1.52 ±0.100 | Thickness (mm): |
| 76.20 | Width (mm): |
| ±0.001 | Line Width Tolerance (µm): |

Optical Properties

| | |
|-------------------------|--|
| Vacuum Deposited Chrome | Coating: |
| 20.00 | Frequency (lp/mm): |
| Opal Glass | Substrate: <input type="checkbox"/> |
| >3.0 | Optical Density OD (Average): |
| 40-20 | Surface Quality: |

Regulatory Compliance

| | |
|---------------------------|------------------------------------|
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |
| Compliant | Reach 235: |

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance