

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #20-138 3-4 DAYS



1



€515,00

ADD TO CART

Qty 1-5

€515,00

Qty 6+

€463,30

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Optical Density OD (Average):
2.0 ±0.15

Substrate: ☐
UV Grade MgF₂

Coating: Metallic Based ND, with Dielectric Over-Coat
Surface Quality: 40-20
Thickness (mm): 3.00 ±0.10
Transmission (%): 1.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 120 - 200
Clear Aperture (%): 80.00
Transmitted Wavefront, P-V: λ/4
Parallelism (arcsec): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View