

20 x 20mm, 800µm Pitch, 1.9° Divergence, Cyl. Microlens Array



Stock **#23-872** 3-4 DAYS

- 1 +

€535,00

ADD TO CART

Qty 1-10
€535,00

Qty 11+
€482,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
24.70 @ 1064nm

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Coating:
Uncoated

Type:

Lens Array (One Sided)
Wavelength Range (nm): 200 - 2200
Dimensional Tolerance (mm): ±0.1
Dimensions (mm): 20.0 x 20.0
Divergence Angle (°): 1.9 (Full Width)
Pitch (µm): 800
Radius R (mm): 11.100
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View