

## 200 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock #57-882 CLEARANCE 1 In Stock

⊖ 1 ⊕ €650<sup>95</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€650,95 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Physical & Mechanical Properties

3.00 Length (inches):

12.7 x 25.4 Pattern Size (mm):

1.10 Thickness (mm):

1.00 Width (inches):

### Optical Properties

**Coating:**  
Vacuum Deposited Chrome  
Fluorescent Peak Excitation @ 365 nm; Fluorescent  
Peak Emission @ 550 nm

**Frequency (lp/mm):**  
200.00

**Substrate:**   
[Fused Silica](#) with Fluorescent Backing

**Optical Density OD (Average):**  
3.00

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 240:**  
[Compliant](#)

## Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
- Ideal for Reticle and Field Calibration Requirements
- Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).

Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.