

TECHSPEC® 200mm Dia., 1.1mm Thick, Uncoated, Gorilla Glass® Window



Gorilla® Glass Windows



Stock **#21-240** 3-4 DAYS

◦ 1 ◦

€95,00

ADD TO CART

Qty 1-5
€95,00
Qty 6+
€73,25
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Chemical Strengthening Cycle (hours):

8
Clear Aperture (%) : 90.00
Clear Aperture CA (mm) : 180.00
Diameter (mm) : 200.00 ±0.25
Thickness (mm) : 1.10 ±0.05
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 7.58 (0 to +300°C)
Density (g/cm³) : 2.39
Edges : Fine Ground and Seamed
Index of Refraction n_d : 1.5
Poisson's Ratio : 0.22
Substrate : Gorilla® Glass
Surface Quality : 80-50
Type : Protective Window
Wavelength Range (nm) : 350 - 2200
Young's Modulus (GPa) : 70

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant