

TECHSPEC[®] 20mm - 30mm Length, C-Mount Fine Focus Tube



Stock #58-756 14 In Stock

-

1

+

€118^{,00}

ADD TO CART

Volume Pricing	
Qty 1-4	€118,00 each
Qty 5-9	€104,40 each
Qty 10-25	€96,40 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Fine Focus Tube

Function:

Extension Tube (Adjustable)

Physical & Mechanical Properties

Extension Length (mm):

20.0 - 30.0

30.0	Outer Diameter (mm):
18.0	Clear Aperture CA (mm):
18.0	Inner Diameter (mm):

Threading & Mounting

M18 x0.5	Barrel Thread:
C-Mount	Thread Type:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

Note: Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

Technical Information

