

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 20mm 355nm, Laser Line λ/20 High Tolerance Right Angle Mirror



Stock #37-650 3-4 DAYS

1 €263,00

ADD TO CART

Qty 1-5

€263,00

Qty 6+

€210,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V): λ/20

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality: 20-10

Length of Legs (mm): 20.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R_{abs} >99.8% @ 355nm @ 45° AOI R_{avg} >99.5% @ 351 - 358nm @ 45° AOI
Coating: Laser Mirror (355nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 355
Length of Hypotenuse (mm): 28.30
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: 1MW/cm² @ 355nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View