

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 20mm, 632.8nm, Lateral Displacement Polarizing Beamsplitter



Lateral Displacement Beamsplitters

Stock #47-191 3-4 DAYS



1



€705,00

ADD TO CART

Qty 1-5

€705,00

Qty 6+

€564,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (arcsec):  
±5

Beam Separation (mm):  
20.00

Clear Aperture (%):  
80.00

|                                                                          |
|--------------------------------------------------------------------------|
| <div>Coating Specification:<br/>R<sub>abs</sub> &lt;0.3% @ 632.8nm</div> |
| <div>Construction:<br/>Prism</div>                                       |
| <div>Design Wavelength DWL (nm):<br/>632.8</div>                         |
| <div>Dimensional Tolerance (mm):<br/>±0.1</div>                          |
| <div>Extinction Ratio:<br/>&gt;1000:1</div>                              |
| <div>P-Polarization Transmission (%):<br/>&gt;95</div>                   |
| <div>Parallelism (arcmin):<br/>&lt;2</div>                               |
| <div>S-Polarization Reflection (%):<br/>&gt;99</div>                     |
| <div>Substrate: <div><div></div><div>N-BK7</div></div></div>             |
| <div>Surface Flatness (P-V):<br/>λ/8</div>                               |
| <div>Surface Quality:<br/>40-20</div>                                    |
| <div>Type:<br/>Linear Polarizer</div>                                    |
| <div>Type of Optics:<br/>Polarizing</div>                                |

Regulatory Compliance

|                                                 |
|-------------------------------------------------|
| <div>RoHS:<br/>Compliant</div>                  |
| <div>Certificate of Conformance:<br/>View</div> |