

TECHSPEC[®] 2.0mm Thick, C-Mount Brass Spacer Ring



Brass Spacer Ring

Stock #03-633 9 In Stock

-

1

+

€11²⁵

ADD TO CART

Volume Pricing	
Qty 1-4	€11,25 each
Qty 5-9	€10,50 each
Qty 10-25	€10,00 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Spacer Ring

Function:

Physical & Mechanical Properties

2.00

Thickness (mm):

Outer Diameter (mm):

29.0	
	Inner Diameter (mm):
25.5	
Threading & Mounting	
	Thread Type:
C-Mount	
Regulatory Compliance	
	RoHS 2015:
Exempt	
	Certificate of Conformance:
View	
	Reach 250:
Contains SVHC(s)	

Product Details

- Fit Over Male C, S, and T-Mount Threads
- Wide Range of Thicknesses Available for Accurate Spacing
- Spacer Ring Kits Available

TECHSPEC® C, S, and T-Mount Brass Spacer Rings fit over the male threads on our C, S, and T-Mount components, extending the overall length of the system. These spacer rings are ideal for making incremental adjustments to component spacing within an optical system. TECHSPEC® C, S, and T-Mount Brass Spacer Rings are available in thicknesses ranging from 0.25mm to 2.0mm, ensuring that application specific spacing is available. Kits of [C-Mount](#) and [S-Mount](#) Spacer Rings with 2 of each size can be found under the “Accessories” tab for this product. These spacer rings can be combined in multiple configurations to achieve the desired spacing distance.

Technical Information

